

FINAL INSPECTION REPORT

1x2 Dual Window Coupler

Item #: TD1315R1A1

SN: T134948

Center Wavelength: 1310 nm / 1550 nm

Coupling Ratio Specification

Tap Output: 0.4% - 1.6%

Signal Output: 98.4% - 99.6%

Bandwidth: ± 40 nm

Maximum Optical Power^a

With Connectors or Bare Fiber: 1 W

Spliced: 5 W

Fiber Type: Corning SMF-28e+

Test Data ^b	1310 nm	1550 nm
Excess Loss ^c	0.07 dB	0.12 dB
Input-Output Path	White (Input) – White (Signal Output)	
Coupling Ratio ^d	99.4%	99.2%
Insertion Loss ^e	0.10 dB	0.15 dB
Input-Output Path	White (Input) – Red (Tap Output)	
Coupling Ratio ^d	0.6%	0.8%
Insertion Loss ^e	22.40 dB	21.33 dB

a. Specifies the maximum power allowed through the component. Performance and reliability under high power conditions must be determined within the user's setup.

b. All values are measured at room temperature without connectors through the white input port.

c. Ratio of the input optical power to the total optical power from all output ports. It is measured at each wavelength.

d. Does not include losses, as this is a measurement of the output power distribution only.

e. Includes both the split of the power between the two outputs, as well as any optical losses in the coupler.

Verified by: _____